

## **SQP Vane Pumps**

## -Low noise intravane pumps for industrial applications







## How to order

(F3-)	SQP2	-21	-86	С	(F)	-(LH)	10
Prefix, fluid compat-	Series	▲ Code	Shaft	Outlet positions	Mounting	Rotation	Design
ibility	SQP1	2, 3, 4, 5, 6, 7, 8, 9,	1-Straight	(Viewed from cover end	Omit	(viewed from	10
None		10, 11, 12, 14	key	pump)	Flange	shaft end of	
Autiwear oil or	SQP2	10, 12, 14, 15, 17,	86-HD.	A-Opposite inlet port	mounting	pump)	
phosphate ester fluid		19, 21	straight key	B-90° CCW from inlet	F-Foot	LH: CCW	
F11-Water-plycol	SQP3	21, 25, 30, 32, 35,		C-Inline with inlet	mounting	-: CW	
F3-		38, 45		D-90° CW from inlet			
Water in oil emulsion	SQP4	42, 45, 50, 57, 60,					
		66, 75					